

PRODUCT ASSEMBLY >

DS-JT-25

DS-JT-50

DS-JT-60



Normal Neutral Pen

DS-JT-25



L*W*H : 97MM*48MM*67MM

Suitable for $\Phi 18$ mm laser , $\Phi 25$ mm Installing cross bar

DS-JT-50



L*W*H : 122MM*48MM*94MM

Suitable for $\Phi 18$ mm laser , $\Phi 50$ mm Installing cross bar

DS-JT-60




L*W*H : 132MM*48MM*104MM

Suitable for $\Phi 18$ mm laser , $\Phi 60$ mm Installing cross bar

Loosen the fixed screw and adjust the left and right distance by two-dimensional translation



Fine tooth screw adjustment combined with high quality spring reset
Make two-dimensional tilt adjustment more accurate



Axial locking screw can prevent laser from loosening due to vibration more effectively



Bracket hole $\Phi 18.3$ mm.
This bracket is suitable for $\Phi 18$ mm laser.